

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191540022
Status: Active
Overview: [Splices](#)
Description: Step Down Butt Splice for 14-22 AWG Wire Blue w/Red Stripe

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Splices
Series 19154
Comments Step down: 14/16 to 18/22 AWG . Blue with Red Stripe
Crimp Quality Equipment Yes
Mil-Spec N/A
MolexKits Yes
Overview [Splices](#)
Product Name Butt - Step Down
UPC 800753108875

Physical
Barrel Type Closed - Brazed
Color - Resin Blue
Flammability 94V-0
Insulation PVC
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PVC
Net Weight 1.730/g
Packaging Type Bag
Temperature Range - Operating -40°C to +105°C
Wire Insulation Diameter 4.45mm max.
Wire Size AWG 14, 16, 18, 20, 22

Electrical
Voltage - Maximum 600V

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number BA-631X

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19154-007



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/21/2016 (20 June 2016) Halogen-Free Status Not Low-Halogen	China RoHS
--	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
19154 Series