



Drawings not to scale
All dimensions in mm

SPECIFICATION

CONTACT FORM/STYLE		Open
SWITCHING VOLTAGE	Max. Vac	24
SWITCHING CURRENT	Max. A	0.1
SWITCHING CAPACITY	Max. VA	1.0
CONTACT RESISTANCE	Max. mΩ	200
SWITCHING DISTANCE	Min. mm	Dependant on magnet
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		Polypropylene

PROXIMITY SENSORS

PART NUMBER
PPS 24

Rev. No.	Revision Note	Date	Signature
B	1998 Catalogue Page 36	1-1-98	RG



BS5750/ISO 9000
Reg. No. FM 21080

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.