

MODEL No.	SC-1080P-BG-VF-BES
Image Sensor	1/2.7" OV 2.1MP CMOS Sensor
Effective Picture Elements (H×V)	1920 X1080
Resolution	1080P
Signal System	PAL / NTSC
Minimum Illumination	0.001 Lux/F1.2
S/N Ratio	More than 50dB
Synchronous System	Internal, Negative sync.
IR Distance	40 Meters (with Φ 5X42PCS Infrared LED)
IR Power On	Photodiode AUTO Control
Video Output	AHD/CVI/CVBS/TVI
Functions	WDR, DNR, UTC
Power/Current	DC12V(+/-10%)/500mA
Lens	2.8-12mm Manual Zoom Lens
Weather Proof	IP66
Dimension (mm)	306(W)X97(H)X110(D)
Weight (g)	1600
Operating Conditions	-10~+50°C RH95% MAX

