


KEMET Part Number: PHE448SB4150JR06
(F448BJ152J2K0C)

Film, Film/Foil Polypropylene, Commercial Grade, PHE448/F448, 1500 pF, 5%, 2,000 V, 85C, Lead Spacing = 15mm



General Information

Dielectric:	Film/Foil Polypropylene
Style:	Radial
Series:	PHE448/F448
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart). Rthha= 82 C/W (85C), 0.2 m/s

Dimensions

L	18mm MAX
H	12.5mm MAX
T	6.5mm MAX
S	15mm +/-0.4mm
LL	6mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	1000

Specifications

Capacitance:	1500 pF
Capacitance Tolerance:	5%
Voltage DC:	2000 VDC, 1480 VDC (105C)
Voltage AC:	700 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.03% 1kHz, 0.05% 10kHz, 0.1% 100kHz
Insulation Resistance:	20 GOhms
Max dVdt:	25,000 V
Inductance:	6 nH