


Film, Metallized Polyester Stacked, Commercial Grade, R82, 0.22 uF, 10%, 250 V, 85C, Lead Spacing = 5mm

**General Information**

Dielectric:	Metallized Polyester Stacked
Style:	Radial
Series:	R82
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

Dimensions

L	7.2mm +0.3mm
H	11mm +0.1mm
T	6mm +0.1mm
S	5mm +/-0.4mm
H0	18mm +/-0.5mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging:	Ammo, 360x340x59mm, Box
Packaging Quantity:	1400

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	10%
Voltage DC:	250 VDC
Voltage AC:	140 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.8% 1kHz, 1.2% 10kHz
Insulation Resistance:	30 GOhms
Max dVdt:	130 V
Inductance:	7 nH