



KEMET Part Number: SMR15225J63B12L16.5CBULK
(F211BM225J063ALG5C)



Film, Metallized PPS, Commercial Grade, SMR/F211, 2.2 uF, 5%, 63 V, 125C, Lead Spacing = 15mm



Dimensions

L	18mm MAX
H	15mm MAX
T	8mm MAX
S	15mm +/-0.4mm
LL	16.5mm +/-0.5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	400

General Information

Dielectric:	Metallized PPS
Style:	Radial
Series:	SMR/F211
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The rated voltage decreases 2%/C between +125C and +150C
Notes:	Case Size = BM

Specifications

Capacitance:	2.2 uF
Capacitance Tolerance:	5%
Voltage DC:	63 VDC
Voltage AC:	40 VAC
Temperature Range:	-55/+150C
Rated Temperature:	125C
Dissipation Factor:	0.15% 1kHz, 0.35% 10kHz
Insulation Resistance:	2.27273 GOhms
Max dVdt:	6 V