LED Lamps and LED Lampholders LED Lampholders can be supplied with or without LEDs



Key Features

Colours and voltages:

- LED lampholders
- Supplied with or without LEDs
- Black or Chrome finish

Colours: Red, Yellow, Green and Blue LEDs (High Intensity is standard. Option of extra super bright).

Voltages: LEDs are available for direct connection to 2.0/2.2V or 12Vdc

For other voltages contact sales.

Terminal	Туре	Sealed	Body Colour	LED Colour	Voltage	Panel Cutout	Approval	Dimensions
W LED fitted A LED not fitted T L LED & Wires fitted	(W) 1047 OO	S Sealed	B Black Blank	R Red Y Red	1 LED Resistor 4 6Vdc LED	6.3 6.3max T85		14.5 +/- 0.36
W LED fitted A LED not fitted J J L LED & Wires fitted	(L) 1048 OO			G Green B Blue	5 12Vdc LED 6 24Vdc LED	8.0 5.5max		2.0 Ø9.5
W LED fitted A LED not fitted TT L LED & Wires fitted	(W) 1050 OO					8.0 7.0max		2.9 010.0
W LED fitted T LED & Wires fitted	(L) 1035 OA					4.5 0.9-1.6		4,30 1.0
W LED fitted T T L ED & Wires fitted	(L) 1036 OA					6.0 0.9-1.6 T85		5.85 1.0
W LED fitted TT L LED & Wires fitted	(L) 1037 OA					6.35 0.9-1.6 T85		0,15 ¥ 1.0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0