# **HANN**Spree

## **HANN**Spad

### **HANNSpad 116 Poseidon**

11.6" IPS Wi-Fi



















11.6" / 29,46 cm

Part. No..: SN12TP1B

#### SIZE, RESOLUTION



11.6" IPS Panel 29,46 cm



1366 x 768

#### CPU, RAM MEMORY



QuadCore CPU ARM Cortex A53 64 bit



2 GB DDR3

#### CAMERA, STORAGE



Dual Camera 2MP/2MP



16 GB

### Wi-Fi, CONNECTIVITY



Dual Band WLAN 802.11 a/b/g/n 2.4 / 5 GHz



Bluetooth 4.0 (LE)

Technical Specifications >>>

# **HANN**Spree

## **HANN**Spad

Name / Part Nr.	HANNSpad Poseidon / SN12TP1B
Screen Size	29.46 cm / 11.6 lnch
Resolution (H x V)	1366 x 768, 16:9 Aspect Ratio
Viewing Angle	178° (V) / 178° (H)
Touchscreen Type	Multi Point Capacitive Touch Panel
CPU	Quad Core CPU MT8163 Cortex ARM A53 64 bit, 1.3 GHz
GPU	Mali 720 MP2
Memory	2GB RAM DDR3L
Storage Internal	16GB eMMC NAND FLASH
Storage External	Micro-SD/Micro-SDHC Card, max. 32GB
WLAN	Wi-Fi IEEE 802.11 a/b/g/n 2.4/5GHz (802.11ac is not supported)
Bluetooth	Bluetooth 4.0 LE
Camera	Front 2MP / Rear 2MP
Microphone	Built-in
Speakers	Built-in, Stereo Speakers 2 x 0.8W, 8 ohm
Headphone Output	3.5mm Stereo Earphone
HDMI	-
GPS	Yes
G-Sensor	Yes
3 Axis Accelerometer	Yes
OTG	Yes
Battery Type	Li-Ion Battery 6.000 mAh, 3.7 Volt
Battery Life	>4.5 hours (1080p Video playback, Wi-Fi On, Brightness 80%, Webcam off, Speaker 80%) >7 hours (1080p Video playback, Wi-Fi Off, Brightness 50%, Webcam off, Speaker 50%)
Power Adaptor	DC 5V, 2A

Operating Temperature	0 ~ 45° Celsius
Operating Humidity	10 ~ 85%
Case Material	Plastic with rubber painting
Product Dimensions	294 x 182 x 10.8 (W x H x D mm)
Packaging Dimensions	332 x 293 x 55 (W x H x D mm)
Net Weight	704 grams
Gross Weight	1214 grams
Control Keys	Power, Volume +/-, Reset
Operating System	Android 6 (Marshmallow)
UI Language	Android default
Accessory	1 Power Adaptor with EU and UK clips, 1 USB Cable (120 cm), 1 OTG Cable (8 cm), Quick Start Guide, Warranty Card
Certification	CE EMC, R&TTE, LVD, RoHS, REACH, WEEE
Packaging	Color retail box
EAN Code	4711404021862

PART. NO.: SN12TP1B





© 2016 HANNSpree, Inc. Specifications and design as well as accessories are subject to change without notice. Screen shots are simulated. Actual products may differ slightly from those illustrated on this promotion material. Please refer to actual samples for final selection. The products displayed on this promotion material may not be available for purchase in your particular country or locality. Please check with your local HANNspree authorized representatives for the availability of specific products in your area. Android, Google, Google Play, and the Google Play logo are trademarks of Google Inc.

IMPORTANT NOTICE: Do not attempt to replace the battery of your HANNSpad yourself, you may damage the battery and this could cause overheating and injury. The lithium-ion battery in your HANNSpad should be replaced only by HANNspree or a HANNspree Authorized Service Provider, and must be recycled or disposed of separately from household waste. Do not incinerate the battery. For more information about battery recycling and replacement, go to http://www.hannspree.eu/en/support/battery-replacement.