

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191990010](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp™ Window Butt Connector for 14-16 AWG Wire, Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Splices](#)
Series [19199](#)
Comments Mil Spec M7928/5-4
Crimp Quality Equipment Yes
Mil-Spec M7928/5-4
Overview [Splices](#)
Product Name Avikrimp™, Butt - Window
UPC 800753046832

Physical
Barrel Type Closed
Color - Resin Blue
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 2.192/g
Packaging Type Adhesive Tape on Reel
Temperature Range - Operating -55°C to +105°C
Wire Insulation Diameter 4.34mm
Wire Size AWG 14, 16
Wire Size mm² 1.00-2.50

Electrical
Voltage - Maximum 300V

Material Info
Engineering Number WB-841T

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-015-001
Sales Drawing SD-19199-003



Series image - Reference only

EU ELV
Not Relevant
EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[19199](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION