



Tungsten Carbide Oval-Head Cutters



Tungsten Carbide Blades

- 80-85 HRC
- Cutting Capacity: 22-32 AWG Steel Wire

**Cut Difficult
Wires
With Ease**

Aven's Tungsten Carbide Oval Head Cutters are designed to cut through difficult materials with ease. The tungsten carbide blades have a hardness rating of 80-85 HRC for exceptional durability. Applications include Guide Wires, Stents, Catheters and Single/Multiple Fillers. Features ergonomic soft grips with dual leaf springs to reduce hand fatigue.

Available with Flush and Semi-Flush cutting finishes.



Tungsten Carbide Blades
80-85 HRC

Stainless Steel Sandblasted Finish

Dual Leaf Springs

ESD Safe Comfort Grips

Part #	Description	Blade
10321TC	Tungsten Carbide Oval Head Cutter with Semi-Flush Blade	
10323TC	Tungsten Carbide Oval Head Cutter with Flush Blade	