

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391002010

Status:


Active

Overview:

Eurostyle™ Two-Screw Barrier Strips

Description:

10.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 10 Circuits



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	Eurostyle™ Two-Screw Barrier Strips
Product Name	Eurostyle™ Two Screw
Type	Barrier Strip
UPC	78172545159
Physical	
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	10.00mm
Pitch - Termination Interface	10.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	10, 12, 14, 16, 18
Electrical	
Current - Maximum per Contact	30.0A
Voltage - Maximum	600V
Material Info	
Old Part Number	M800-02-10-5-M1
Reference - Drawing Numbers	
Sales Drawing	SD-39100-013

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION