

General Information

Extended Product Type:	PL5
Product ID:	1SNK900618R0000
EAN:	3472599097490
Catalog Description:	PL5 Protecting Cover - Transparent
Long Description:	- Prohibit access to the screw clamps, - Indicate live circuits.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Protecting Covers

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097
Color:	Transparent

Dimensions

Product Net Height:	49.2 mm
Product Net Length:	25.05 mm
Product Net Depth:	25.1 mm
Product Net Weight:	1.5 g
Product Net Width:	5.2 mm

Technical

Spacing:	5.2 mm
Function:	Protecting Covers
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polycarbonate
Recommended Screw Driver:	4 mm
Suitable For:	ZS4 ZS4-R1 ZS4-S ZS4-SP ZS4-SP-T2 ZS4-S-T

Technical UL/CSA

Flammability According to UL94:	V2
---------------------------------	----

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160021D0201
RoHS Information:	1SND230500F0202

Classifications

E-nummer:	2925166
Object Classification Code:	X

Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	243 mm
Package Level 1 Gross Weight:	0.015 kg
Package Level 1 EAN:	3472599097490
Package Level 2 Units:	1500 piece
Package Level 3 Units:	72000 piece
Product Packing Type:	Bag
Package Level 1 Units:	10 piece

