

General Information

Extended Product Type:	TP4
Product ID:	1SNK900205R0000
EAN:	3472599097322
Catalog Description:	TP4 Test Adapter for test plugs DIA 4 mm .16 in - Dark Grey
Long Description:	- Isolated test adapter that enables individual voltage control, - Direct plug-in solution into the jumpers channels, - Compatible with standard insulated or non isolated test plugs DIA 4 mm 0.157 in, - Withstand more than 10000 operations according to ABB test standards.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Test Adapters

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010
Color:	Dark Grey

Dimensions

Product Net Height:	7.6 mm
Product Net Length:	56.63 mm
Product Net Depth:	56.6 mm
Product Net Weight:	2.4 g
Product Net Width:	7.6 mm

Technical

Spacing:	7.6 mm
Function:	Test Adapters
Rated Current (I_n):	Main Circuit 16 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK2.5-22 ZDK4-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZDS4-22-R1 ZK10 ZK10-3P ZK10-PE ZK10-PE-3P ZK16 ZK16-3P ZK16-PE ZK16-PE-3P ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-S-4P ZK2.5-SF ZK2.5-SF-R ZK2.5-SP

ZK2.5-SP-4P
 ZK2.5-S-R1
 ZK4
 ZK4-3P
 ZK4-4P
 ZK4-PE
 ZK4-PE-3P
 ZK4-PE-4P
 ZK6
 ZK6-3P
 ZK6-PE
 ZK6-PE-3P
 ZP2.5
 ZP2.5-3P
 ZP2.5-4P
 ZP2.5-D1
 ZP2.5-D2
 ZP2.5-PE
 ZP2.5-PE-3P
 ZP2.5-PE-4P
 ZS10
 ZS10-PE
 ZS10-SF
 ZS10-SF-R
 ZS10-S-R2
 ZS16
 ZS16-PE
 ZS25
 ZS25-PE
 ZS4
 ZS4-D1
 ZS4-D2
 ZS4-D2-S
 ZS4-D2-SF1
 ZS4-D2-SF1-R
 ZS4-D2-S-T
 ZS4-D-CH
 ZS4-PE
 ZS4-PE-R2
 ZS4-R2
 ZS4-SF
 ZS4-SF-R
 ZS4-SF-T
 ZS4-SP-R1
 ZS4-SP-T2-R1
 ZS4-S-R1
 ZS4-S-R2
 ZS4-S-T-R1
 ZS4-T3
 ZS4-T3-R1
 ZS6
 ZS6-3S
 ZS6-3S-PE
 ZS6-4S
 ZS6-4S-PE
 ZS6-D1
 ZS6-D1-PE
 ZS6-D2
 ZS6-D2-PE
 ZS6-PE
 ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage	Main Circuit 600 V
UL/CSA:	

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160036D0201
RoHS Information:	1SND230505F0202

Classifications

E-nummer:	2925156
Object Classification Code:	X

Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	243 mm
Package Level 1 Gross Weight:	0.048 kg
Package Level 1 EAN:	3472599097322
Package Level 2 Units:	2000 piece
Product Packing Type:	Bag
Package Level 1 Units:	20 piece

