

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980198](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC® Multi-Hole Strain Relief, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 6.35mm (.250")

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130098](#)
Comments Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.

Eye Type N/A
NEMA Rating NEMA 6P
O-Ring Yes
Overview [Strain-Relief Cord Grips](#)
Product Name MAX-LOC®
Type Strain Relief Grip
UPC 78678818945
Use With 1/2" NPT MAX-LOC® Lock Nut [130099-0143](#)
Woodhead Yes

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter 6.35mm (.250")
Color - Grommet Yellow
Gender Male
Material - Body Nylon
Material - Grip N/A
Mesh Length N/A
Number of Holes 2 or 3
Thread Size 1/2" NPT

Material Info

Old Part Number 5594-005W

Reference - Drawing Numbers

Sales Drawing SD-130098-196



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
ELV Not Reviewed

Search Parts in this Series

[130098](#) Series