

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348993021](#)
Status: **Active**
Overview: MXP120™ Sealed Connector System
Description: MXP120™ Sealed Male Blade Connector with 7.00mm Clip-Slot, 3 Circuit, Light Gray Housing, Key B

Documents:

3D Model	Application Specification AS-34900-0001-CH (PDF)
Drawing (PDF)	Packaging Specification PK-31301-898 (PDF)
Product Specification PS-34900-0001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34900-0001 (PDF)	Product Literature (PDF)



General

Product Family	Crimp Housings
Series	34899
Application	Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120™ Sealed Connector System
Polarization	B
Product Literature Order No	987650-7994
Product Name	MXP120™ Sealed
UPC	887191680507

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	4.512/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-34900-0001, AS-34900-0001-CH
Packaging Specification	PK-31301-898
Product Specification	PS-34900-0001
Sales Drawing	SD-34899-2001, SD-34899-6001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Relevant

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

Search Parts in this Series

[34899 Series](#)

Mates With

MXP120™ Female Receptacle [34900-3121](#)

Use With

1.2 CB SWS from Tyco