

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5011933000

Status:

Active

Overview:

Pico-Clasp™ Wire-to-Board Connectors

Description:

1.00mm Pitch Pico-Clasp™ Wire-to-Board Crimp Terminal, 28-32 AWG, Gold Plating

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5011890000 (PDF)	

General	
Product Family	Crimp Terminals
Series	501193
Application	Signal
Crimp Quality Equipment	Yes
Overview	Pico-Clasp™ Wire-to-Board Connectors
Product Name	Pico-Clasp™
UPC	884982400993
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Net Weight	8.600/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80mm max.
Wire Size AWG	28, 30, 32
Wire Size mm²	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	5011890000
Sales Drawing	SD-501193-003

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

501193 Series

Use With

501189 Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for 1.00mm Pitch Wire-to-Board Crimp Terminal	0639019400
Extraction Tool	0638131700
Hand Crimp Tool for 1.00mm Wire-to-Board Crimp Terminal, 28-32 AWG Wire	0638191500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION