


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930336](#)
Status: **Active**
Description: RING VERSAKRIMP (H-382-12) SPM

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19193
Crimp Quality Equipment	Yes
Product Family	Ring and Spade Terminals
UPC	800755052121
Physical	
Net Weight	30.562/g
Plating min: Mating (µin)	100
Plating min: Mating (µm)	2.5
Plating min: Termination (µin)	100
Plating min: Termination (µm)	2.5
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	H-382-12
Reference - Drawing Numbers	
Sales Drawing	SD-19193-021



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/21/2016 (20 June 2016) Halogen-Free Status Low-Halogen	China RoHS
--	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS ELV	Green Image Not Relevant
-------------------	-----------------------------

Search Parts in this Series
[19193](#) Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	0192860117
Die Set (large) for the HHLS Hydraulic Crimper	0192900011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION