

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301040041](#)  
**Status:** **Active**  
**Overview:** Specialty Lighting  
**Description:** Haztex® Incandescent Hazardous and Wet Location Hand Lamp Only, 100W

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR39801  
 UL E30252

**General**

Product Family Portable Lighting  
 Series [130104](#)  
 Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)  
 NEMA Configuration N/A  
 NEMA Rating NEMA 4X  
 Outlet None  
 Overview [Specialty Lighting](#)  
 Product Literature Order No 987650-8052  
 Product Name Haztex®  
 Type Hand Lamps, Specialty Light  
 UPC 78678861430  
 Woodhead Yes

**Physical**

Cord Length - Primary N/A  
 Cord Length - Secondary N/A  
 Depth 127.00mm (5.000")  
 Duty Hazardous, Wet Location  
 Guard Included No  
 Guard Type N/A  
 Height 419.10mm (16.500")  
 Length N/A  
 Material - Globe Tempered Soda-Lime Glass  
 Material - Guard Cast Aluminum  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Old Part Number 61430



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

**Search Parts in this Series**

[130104 Series](#)