

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936013770](#)

**Status:** **Active**

**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)

**Description:** GWconnect® STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 24B «104x27», Extended M25 Thread, Grey

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Component Size	24B «104X27»
Component Type	Double Lever Hood
IP Rating	IP66, IP69
Overview	<a href="#">GWconnect® Heavy Duty Connectors (HDC)</a>
Product Category	Heavy Duty Connectors
Product Name	GWconnect®
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191860107
Use With	Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

**Physical**

Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Number of Pegs	4
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

**Electrical**

Voltage - Maximum 500V

**Material Info**

Old Part Number 7824.6573.0

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[93601](#) Series