

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202440002

Status:

Active

Overview:

Description:

Micro-Change® (M12) Circular Hybrid Technology (CHT) Female Receptacle, M16x1.5mm Back Panel Mount, 8 Pole (4 Signal, 4 Power)

Agency Certification	
UL	E218123
General	
Product Family	Industrial Receptacles
Series	120244
IP Rating	IP67
Overview	brad_circular_hybrid_technology_cht_connector
Product Name	CHT, Micro-Change® (M12)
Type	Adapter
UPC	884982666979
Physical	
Coupling Type	External Thread
Gender	Female
Keyway	Dual
Length	N/A
Material - Component	Stainless Steel Type 303
Mounting Thread Size	M12
Net Weight	22.091/g
Orientation	Straight
Panel Mount	N/A
Poles	8
Temperature Range - Operating	-25°C to +75°C
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	6.0A
Voltage - Maximum	30V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-120244-002

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with

Exemption 6(c)

REACH SVHC

Not Contained Per -

ED/108/2014 (17 Dec

2014)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

120244 Series

Mates With

120244 Micro-Change® (M12) Circular Hybrid Technology (CHT) Double-Ended Cordset

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION