

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200910004](#)
Status: **Active**
Overview: [Brad® Nano-Change® (M8) Products](#)
Description: Nano-Change® (M8) Attachable Connectors, Straight Male, 3 Poles

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	120091
IP Rating	IP67
MolexKits	Yes
Overview	Brad® Nano-Change® &#40;M8&#41; Products
Product Name	Nano-Change® (M8)
Type	Field Attachable Connector
UPC	78678832308

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold over Nickel
Net Weight	8.260/g
Orientation	Straight
Poles	3
Temperature Range - Operating	0°C to +80°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Old Part Number	N03MA03124
-----------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-120091-001
---------------	---------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[120091](#) Series