

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100035](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Wet Location 70W Metal Halide Magnet Mount Area Light, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E174254

General

Product Family Portable Lighting
 Series [130110](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 3
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Literature Order No 987650-8054
 Product Name Woodhead®
 Type Wide Area Lamps
 UPC 78678829248
 Woodhead Yes

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary N/A
 Depth 207.26mm (8.160")
 Duty Wet Location
 Guard Included No
 Guard Type N/A
 Height 264.16mm (10.400")
 Length 228.60mm (9.000")
 Material - Globe Clear Polycarbonate
 Material - Guard N/A
 Mounting Style Magnet
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Metal Halide - Probe Start
 Cord Type - Primary 16/3 SJTOW
 Lamp Type MH70
 Lamp Wattage - Maximum 70W
 Lumens 3600
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 8565-MH



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[130110 Series](#)