

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934447111](#)
Status: **Active**
Overview: ML-XT™ Sealed Connection System
Description: ML-XT™ Sealed 18 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option A, Black

Documents:

Drawing (PDF)	Packaging Specification 934430002 (PDF)
Product Specification 934430010 (PDF)	Packaging Specification 934430010 (PDF)
Application Specification 934430010 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT™ Sealed Connection System
Product Name	ML-XT™
UPC	889056263733

Physical

Circuits (maximum)	18
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	17.440/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002, 934430010
Product Specification	934430010
Sales Drawing	934430070



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[93444 Series](#)

Mates With

ML-XT™ Sealed 18 Circuit Plug Housing
[93445-7111](#)

Use With

ML-XT™ Male (Pin) Terminal [84524-0004](#) (Nickel), ML-XT™ Male (Pin) Terminal [84524-0014](#) (Selective Gold), ML-XT™ Blind Cavity Plug [93494-1000](#)