

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301090027](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Pro-Yellow® Nylon 150W Incandescent Hand Lamp with Side Outlet and Switch, Grips Molded, Cord Type 16/3 SJTW, Cord Length 15.24m (50.0'), Easy Access Metal Guard

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

UL      E59049

**General**

Product Family      Portable Lighting  
 Series      [130109](#)  
 NEMA Configuration      NEMA 5-15  
 Outlet      Side  
 Overview      [Hand Lamps](#)  
 Product Literature Order No      987650-8053  
 Product Name      Pro-Yellow®  
 Type      Hand Lamps  
 UPC      78678850116  
 Woodhead      Yes

**Physical**

Cord Length - Primary      15.24m (50.0')  
 Cord Length - Secondary      N/A  
 Depth      N/A  
 Duty      Commercial  
 Guard Included      No  
 Guard Type      N/A  
 Height      N/A  
 Length      N/A  
 Material - Guard      #8 Gauge Zinc-plated Steel  
 Mounting Style      Hand Held  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Incandescent  
 Cord Type - Primary      16/3 SJTW  
 Lamp Type      A21  
 Lamp Wattage - Maximum      150W  
 On/Off Switch      Yes  
 Voltage (Fixture) - Maximum      120VAC 60 HZ

**Material Info**

Old Part Number      WT6C-50



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[130109](#) Series