



Datasheet for part number DASF15PK87

Our Catalog Part Number: DASF-15P-K87
Our Global Manufacturing Part Number: 115153-0061
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*SF

Product Datasheet	
General	Speedy D connector terminate ribbon cables without stripping and without splicing
Wire Gauge Range AWG	AWG 26-28
Mating Cycles	50
Dielectric Withstanding Voltage	780 VAC at sea level
Current Rating	1.5 A max
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	15 contacts size 20
Gender	Pin
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Contact Termination	IDC
Mounting Methode	.120" (3,05mm) Through Hole
Accessory	supplied without strain relief