

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1301080088**
Status: **Active**
Overview: Hand Lamps
Description: Super-Safeway™ 30W Fluorescent Hand Lamp with Cord Ballast Location and Switch, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series 130108
NEMA Configuration NEMA 5-15
Outlet None
Overview Hand Lamps
Product Literature Order No 987650-8053
Product Name Super-Safeway™
Type Hand Lamps
UPC 78678861264
Woodhead Yes

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 58.40mm (2.300")
Duty Industrial
Guard Included No
Guard Type N/A
Height N/A
Length 882.65mm (34.750")
Material - Globe Butyrate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 18/3 SJTW
Lamp Type F30/T8
Lamp Wattage - Maximum 30W
Lumens 2000
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1015-3



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130108 Series