

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301020212](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway™ Rubber Hand Lamp with Nylon Guard

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR85374

**General**

Product Family      Portable Lighting  
 Series      [130102](#)  
 NEMA Configuration      N/A  
 Outlet      None  
 Overview      [Hand Lamps](#)  
 Product Literature Order No      987650-8053  
 Product Name      Super-Safeway™  
 Type      Hand Lamps  
 UPC      78678899200  
 Woodhead      Yes

**Physical**

Cord Length - Primary      N/A  
 Cord Length - Secondary      N/A  
 Depth      127.00mm (5.000")  
 Duty      Industrial  
 Guard Included      No  
 Guard Type      N/A  
 Height      400.05mm (15.750")  
 Length      N/A  
 Material - Guard      Nylon  
 Mounting Style      Hand Held  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Incandescent  
 Cord Type - Primary      16/3 SOOW  
 Lamp Type      A21  
 Lamp Wattage - Maximum      100W  
 Lumens      1000  
 On/Off Switch      No  
 Voltage (Fixture) - Maximum      240V

**Material Info**

Old Part Number      118



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[130102 Series](#)