

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300190001](#)  
**Status:** **Active**  
**Description:** Die Block 2 Pole Angle Receptacle, Yellow

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E46237

**General**

Product Family Industrial Receptacles  
 Series [130019](#)  
 IP Rating N/A  
 Product Name Die Block  
 Type Die Block  
 UPC 78678822801

**Physical**

Coupling Type Push to Lock  
 Gender Female  
 Keyway N/A  
 Length N/A  
 Material - Component Nickel-plated Brass  
 Mounting Thread Size N/A  
 Orientation N/A  
 Panel Mount N/A  
 Poles 2  
 Temperature Range - Operating N/A  
 Wire Size AWG N/A  
 Wire/Cable Type N/A

**Electrical**

Current - Maximum per Contact 25.0A  
 Voltage - Maximum 600V AC

**Material Info**

Old Part Number 22801

**Reference - Drawing Numbers**

Sales Drawing SD-130019-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant/Exempted**

**REACH SVHC**

Not Contained Per -  
 ED/108/2014 (17 Dec  
 2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS 50 Image  
 ELV Not Relevant

**Search Parts in this Series**

[130019 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**