

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1502010007](#)  
**Status:** **Active**  
**Overview:** [Ditto™ Wire-to-Wire Interconnects](#)  
**Description:** [Ditto™ Genderless Crimp Housing, Positive Lock, 7 Circuit, Glow Wire Capable](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-150170-0000 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">150201</a>
Application	Power, Wire-to-Wire
Overview	<a href="#">Ditto™ Wire-to-Wire Interconnects</a>
Product Name	Ditto™
UPC	889056215787

**Physical**

Circuits (maximum)	7
Color - Resin	Natural (White)
Gender	Genderless
Glow-Wire Compliant	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.904/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Temperature Range - Operating	-40°C to +105°C, -40°C to +80°C, See Product Specification


**Electrical**

Current - Maximum per Contact	4.3A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-150170-0000
Sales Drawing	SD-150201-0000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

**China RoHS**

Not Reviewed  
Not Reviewed

**Search Parts in this Series**

[150201](#) Series

**Mates With**

Ditto™ Genderless Crimp Housing [150201](#)

**Use With**

Ditto™ Genderless Terminals [150200](#)