

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348993040

Status:

Active

Overview:

MXP120™ Sealed Connector System

Description:

MXP120™ Sealed Male Blade Connector with 11.00mm Clip-Slot, 3 Circuit, Black Housing, Key A



Documents:

3D Model

Drawing (PDF)

Product Specification PS-34900-0001 (PDF)

Application Specification AS-34900-0001 (PDF)

Application Specification AS-34900-0001-CH (PDF)

Packaging Specification PK-31301-898 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General	
Product Family	Crimp Housings
Series	34899
Application	Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120™ Sealed Connector System
Polarization	A
Product Literature Order No	987650-7994
Product Name	MXP120™ Sealed
UPC	887191911083
Physical	
Circuits (maximum)	3
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	4.096/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +125°C

Electrical	
Current - Maximum per Contact	13.0A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-34900-0001, AS-34900-0001-CH
Packaging Specification	PK-31301-898
Product Specification	PS-34900-0001
Sales Drawing	SD-34899-2001, SD-34899-6001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed

Search Parts in this Series

34899 Series

Mates With

MXP120™ Female Receptacle 34900-3120

Use With

1.2 CB SWS from Tyco

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION