

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348978200

Status:

Active

Overview:

Mini50™ Connection Systems

Description:

Mini50™ Unsealed Right Angle SMT Header, Dual Row, 20 Circuit, Polarization Option A, Black, Tape and Reel

Documents:	
3D Model	Product Specification PS-34791-020 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34897
Application	Power, Signal, Wire-to-Board
Overview	Mini50™ Connection Systems
Product Name	Mini50™
UPC	887191459301
Physical	
Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	3.432/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-34791-020
Sales Drawing	GU5T-14F262-DA, SD-34897-001

[EU ELV](#)
Compliant

[EU RoHS](#)
Compliant

[China RoHS](#)

[REACH SVHC](#)
Not Contained Per
-ED/79/2015 (17
December 2015)

[Halogen-Free](#)
Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant

Search Parts in this Series
[34897](#) Series

Mates With
34824 Mini50™ Unsealed Dual Row
Receptacle

This document was generated on 05/17/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION