# RB121-115VUC



#### **General Information**

 Extended Product Type:
 RB121-115VUC

 Product ID:
 1SNA645003R0500

 EAN:
 4013614507731

Catalog Description:RB121-115VUC Interface relay R600 1c/o,A1-A2=115VAC/DC,250V/10mA-6ALong Description:Screw relay RB121A 115vac/dc : 115vac-dc input / 1SPDT 10 mA upto 6A with led

### Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

# Ordering

Minimum Order Quantity:10 pieceCustoms Tariff Number:85364900EAN:4013614507731

#### **Dimensions**

Product Net Height:67.5 mmProduct Net Depth:70 mmProduct Net Weight:0.02 kgProduct Net Width:6 mm

# **Container Information**

Package Level 1 Width: 73 mm

Package Level 1 Height: 71 mm

Package Level 1 Length: 80 mm

Package Level 1 Gross Weight: 0.23 kg

Package Level 1 EAN: 3472596450038

Package Level 1 Units: 10 piece

### **Technical**

Sub-Function:Relay with built in LEDOutput:1 c/o (SPDT) contactOutput Signal:12 ... 250 V AC / 10 mA ... 6 A

Rated Control Supply Voltage (U<sub>s</sub>): 115 V AC/DC Terminal Type: Screw Terminals

**Function:** Boxed interface relay R600

#### **Environmental**

RoHS Status: Following EU Directive 2011/65/EC

# **Certificates and Declarations (Document Number)**

 Instructions and Manuals:
 1SVC645000M9000

 CB Certificate:
 CB\_DK-53188-UL

 CSA Certificate:
 CSA\_254821

 cUR Certificate:
 cUR\_E352056

 Data Sheet, Technical Information:
 1SVC117001D0200

 Declaration of Conformity - CE:
 1SVD982016-0000

**EAC Certificate:** EAC\_RU\_C-FR.ME77.B.01634

 LR Certificate:
 LR\_16\_20068

 RoHS Information:
 1SVD982016-4400

 UR Certificate:
 UR\_E352056

# Classifications

ETIM 4: EC001437 - Switching relay
ETIM 5: EC001437 - Switching relay
ETIM 6: EC001437 - Switching relay
eClass: 7.0 27371601

UNSPSC: 39121500 Object Classification Code: K

