

MC612PA 1->10 (x10) Vertical



General Information

Extended Product Type:	MC612PA 1->10 (x10) Vertical
Product ID:	1SNK150012R0000
EAN:	3472599999435
Catalog Description:	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Vertical
Long Description:	MC612PA Terminal Block Markers pre-printed : 1->10 (x10) Vertical White.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Markers and Marking Systems » Terminal Block Markers

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	39269097
Color:	White

Dimensions

Product Net Height:	12 mm
Product Net Length:	5.6 mm
Product Net Depth:	5.6 mm
Product Net Weight:	11 g
Product Net Width:	6 mm

Technical

Spacing:	6 mm
Function:	Pre-printed marker card
Insulation Material:	Polyamide

Technical UL/CSA

Flammability According to UL94:	V2
---------------------------------	----

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160008D0201
Declaration of Conformity - CE:	1SND225156C1000
RoHS Information:	1SND230504F0204

Classifications

E-number:	2967594
ETIM 4:	EC000761 - Labelling for terminal block
ETIM 5:	EC000761 - Labelling for terminal block
ETIM 6:	EC000761 - Labelling for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	120 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.011 kg
Package Level 1 EAN:	3472599999435
Package Level 2 Units:	600 piece
Package Level 3 Units:	14400 piece
Package Level 1 Units:	1 piece

