RB121PG-5VDC



General Information Extended Product Type: RB121PG-5VDC Product ID: 1SNA645036R2500 EAN: 4013614507991 Catalog Description: RB121PG-5VDC Interface relay R600 1c/o,A1-A2=5VDC,250V/3mA-6A Long Description: Screw relay RB121 5vdc : 5vdc input / 1SPDT 1 mA upto 6A with led

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900
EAN:	4013614507991
Dimensions	
Product Net Height:	67.5 mm
Product Net Depth:	70 mm
Product Net Weight:	0.02 kg
Product Net Width:	6 mm
Container Information	
Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	3472596450366
Package Level 1 Units:	10 piece
Technical	
Sub-Function:	Relay with built in LED
Output:	1 c/o (SPDT) contact
Output Signal:	5 250 V AC / 1 mA 6 A
Rated Control Supply Voltage (U_s):	5 V DC
Terminal Type:	Screw Terminals
Function:	Boxed interface relay R600

Environmental

RoHS Status:

ETIM 6:

eClass:

UNSPSC:

Object Classification Code:

tee and Declarations (Decument Number)

Certificates and Declarations (Document Number)		
Instructions and Manuals:	1SVC645000M9000	
CB Certificate:	CB_DK-53188-UL	
CSA Certificate:	CSA_254821	
cUR Certificate:	cUR_E352056	
Data Sheet, Technical Information:	1SVC117001D0200	
Declaration of Conformity - CE:	1SVD982016-0000	
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634	
LR Certificate:	LR_16_20068	
RoHS Information:	1SVD982016-4400	
UR Certificate:	UR_E352056	
Classifications		
ETIM 4:	EC001437 - Switching relay	
ETIM 5:	EC001437 - Switching relay	

Following EU Directive 2011/65/EC

EC001437 - Switching relay

7.0 27371601

39121500

Κ

