

General Information

Extended Product Type:	ES-TC8
Product ID:	1SNK900104R0000
EAN:	3472599097278
Catalog Description:	ES-TC8 Spacer - Dark Grey
Long Description:	ES-TC8 Spacer - Dark Grey.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Spacers

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097
Color:	Dark Grey

Dimensions

Product Net Height:	34.2 mm
Product Net Length:	42.5 mm
Product Net Depth:	42.5 mm
Product Net Weight:	1.4 g
Product Net Width:	2.8 mm

Technical

Spacing:	2.8 mm
Function:	Spacers
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ES-TC TC5 ZK6 ZK6-3P ZK6-PE ZK6-PE-3P ZS10 ZS10-PE ZS10-SF ZS10-SF-R ZS10-S-R2 ZS4-D2-SF1 ZS4-D2-SF1-R

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160042D0201
RoHS Information:	1SND230503F0202

Classifications

E-nummer:	2925151
Object Classification Code:	X

Container Information

Package Level 1 Width:	85 mm
Package Level 1 Length:	100 mm

Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.014 kg
Package Level 1 EAN:	3472599097278
Package Level 2 Units:	2000 piece
Package Level 2 Width:	200 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	200 mm
Product Packing Type:	Bag
Package Level 1 Units:	10 piece

