

General Information

Extended Product Type:	CO
Product ID:	1SNK900604R0000
EAN:	3472599163706
Catalog Description:	CO Protecting Cover - Transparent
Long Description:	- Restrict access to your assembly with the protecting cover CO installed with KCO mounting kit (2 end stops, 2 sealing accessories), - Compatible with SNK feed-through terminal blocks up to 35 mm² 0 AWG.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Protecting Covers
--

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	39269097
Color:	Transparent

Dimensions

Product Net Height:	77 mm
Product Net Length:	30.2 mm
Product Net Depth:	30.2 mm
Product Net Weight:	300 g
Product Net Width:	1000 mm

Technical

Spacing:	1000 mm
Function:	Protecting Covers
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	PVC
Suitable For:	C6/8.ST4 D35/16.PEN.2L ZP2.5 ZP2.5-D2 ZP2.5-PE ZP2.5-S ZP2.5-SP ZS10 ZS10-PE ZS10-PE-R1 ZS10-R1 ZS10-S ZS10-ST ZS10-ST-1 ZS10-ST-T4 ZS16 ZS16-PE ZS25 ZS25-PE ZS35 ZS35-PE ZS35-PEN ZS4 ZS4-PE ZS4-R1 ZS4-S ZS4-SF1 ZS4-SF1-R ZS4-SF1-T ZS4-SP ZS4-SP-T2 ZS4-S-R3 ZS4-S-T ZS6 ZS6-PE ZS6-S

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +80 °C Storage -55 ... +80 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160020D0201
RoHS Information:	1SND230500F0202

Classifications

E-nummer:	E2925163
Object Classification Code:	X

Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	243 mm
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 EAN:	3472599163706
Package Level 3 Units:	50 piece
Product Packing Type:	Bag
Package Level 1 Units:	1 piece

