



General Information

Extended Product Type:	JB6-3
Product ID:	1SNK906303R0000
EAN:	3472599097629
Catalog Description:	JB6-3 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars
--

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	15 mm
Product Net Length:	26.8 mm
Product Net Depth:	26.8 mm
Product Net Weight:	2.1 g
Product Net Width:	6 mm

Technical

Spacing:	6 mm
Function:	Jumper Bars
Rated Current (I _n):	Main Circuit 41 A
Rated Short-time Withstand Current (I _{cw}):	for 1 s 720 A
Rated Voltage (U _r):	1000 V
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1.3 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK4-22 ZDS4-22-R1 ZK2.5-SF ZK2.5-SF-R ZK2.5-S-R1 ZK4 ZK4-3P ZK4-4P ZK4-PE ZK4-PE-3P ZK4-PE-4P ZK6 ZK6-3P ZK6-PE ZK6-PE-3P ZS4-PE-R2 ZS4-R2 ZS4-SF ZS4-SF-R ZS4-SF-T ZS4-SP-R1 ZS4-SP-T2-R1 ZS4-S-R1 ZS4-S-R2 ZS4-S-T-R1 ZS4-T3-R1 ZS6 ZS6-3S ZS6-3S-PE

ZS6-4S
ZS6-4S-PE
ZS6-D1
ZS6-D1-PE
ZS6-D2
ZS6-D2-PE
ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162004A1706
CB Certificate:	1SND161025A0203
Data Sheet, Technical Information:	1SNK160029D0201
RoHS Information:	1SND230499F0202

Classifications

E-nummer:	2925373
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	50 mm
Package Level 1 Length:	117 mm
Package Level 1 Height:	50 mm
Package Level 1 Gross Weight:	0.105 kg
Package Level 1 EAN:	3472599097629
Package Level 2 Units:	1500 piece
Package Level 3 Units:	144000 piece
Package Level 1 Units:	50 piece

