

## General Information

|                        |                                                                                        |
|------------------------|----------------------------------------------------------------------------------------|
| Extended Product Type: | EK10                                                                                   |
| Product ID:            | 1SNK710910R0000                                                                        |
| EAN:                   | 3472597109102                                                                          |
| Catalog Description:   | EK10 End Section - Dark Grey                                                           |
| Long Description:      | - Compatible with ZK10, ZK10-PE, ZK16 and ZK16-PE PI-Spring screwless terminal blocks. |

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

## Ordering

|                         |           |
|-------------------------|-----------|
| Minimum Order Quantity: | 20 piece  |
| Customs Tariff Number:  | 39269097  |
| Color:                  | Dark Grey |

## Dimensions

|                     |         |
|---------------------|---------|
| Product Net Height: | 80.5 mm |
| Product Net Depth:  | 41.7 mm |
| Product Net Weight: | 3.3 g   |
| Product Net Width:  | 2 mm    |

## Technical

|                       |                                                              |
|-----------------------|--------------------------------------------------------------|
| Spacing:              | 2 mm                                                         |
| Function:             | End Sections                                                 |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material:  | Polyamide                                                    |
| Suitable For:         | ZK10<br>ZK10-PE<br>ZK16<br>ZK16-PE                           |

## Technical UL/CSA

|                                 |    |
|---------------------------------|----|
| Flammability According to UL94: | V0 |
|---------------------------------|----|

## Environmental

|                          |                                                      |
|--------------------------|------------------------------------------------------|
| RoHS Status:             | Following EU Directive 2011/65/EC                    |
| Ambient Air Temperature: | Operation -55 ... +110 °C<br>Storage -55 ... +110 °C |

## Certificates and Declarations (Document Number)

|                                    |                 |
|------------------------------------|-----------------|
| Instructions and Manuals:          | 1SNK160027C0201 |
| Data Sheet, Technical Information: | 1SNK160027C0201 |
| RoHS Information:                  | 1SND230535F0201 |

## Classifications

|                             |   |
|-----------------------------|---|
| Object Classification Code: | X |
|-----------------------------|---|

## Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Width:        | 130 mm        |
| Package Level 1 Length:       | 280 mm        |
| Package Level 1 Height:       | 0 mm          |
| Package Level 1 Gross Weight: | 0.085 kg      |
| Package Level 1 EAN:          | 3472597109102 |
| Package Level 2 Units:        | 1800 piece    |
| Package Level 2 Width:        | 300 mm        |
| Package Level 2 Length:       | 300 mm        |
| Package Level 2 Height:       | 400 mm        |
| Product Packing Type:         | Bag           |
| Package Level 1 Units:        | 20 piece      |

