

General Information

Extended Product Type: JB8-10

 Product ID:
 1SNK908310R0000

 EAN:
 3472599097711

Catalog Description: JB8-10 Jumper Bar - Orange

Long Description: Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut

poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, -

Perfectly adapted to low level electrical contact (20mA, 50mV).

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

Minimum Order Quantity:20 pieceCustoms Tariff Number:85369010Color:Orange

Dimensions

Product Net Height: 77.6 mm

Product Net Length: 27.8 mm

Product Net Depth: 27.8 mm

Product Net Weight: 14.2 g

Product Net Width: 8 mm

Technical

Spacing:8 mmFunction:Jumper BarsRated Current (In):Main Circuit 57 A

Rated Short-time Withstand Current for 1 s 1200 A

(I_{cw}):

(U_{imp}):

Dielectric Test Voltage: 2200 V
Pollution Degree: 3

Power Loss: 1.8 W

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Insulation Material:PolyamideSuitable For:ZK6

ZK6-3P ZK6-PE ZK6-PE-3P ZS10 ZS10-SF ZS10-SF-R ZS10-S-R2 ZS4-D2-SF1 ZS4-D2-SF1-R

Technical UL/CSA

Flammability According to UL94: V0

Maximum Operating Voltage Main Circuit 600 V

UL/CSA:

Environmental

Resistance to Vibrations acc. to IEC Compliant

60068-2-6:

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Ambient Air Temperature: Operation -55 ... +110 °C

Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

 Instructions and Manuals:
 1SNK160027C0201

 ATEX Certificate:
 1SND162004A1706

 CB Certificate:
 1SND161018A0202

 Data Sheet, Technical Information:
 1SNK160030D0201

 RoHS Information:
 1SND230499F0202

Classifications

E-nummer:	2925382
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	50 mm
Package Level 1 Length:	117 mm
Package Level 1 Height:	50 mm
Package Level 1 Gross Weight:	0.284 kg
Package Level 1 EAN:	3472599097711
Package Level 2 Units:	600 piece
Package Level 3 Units:	57600 piece
Package Level 1 Units:	20 piece

