

## General Information

Extended Product Type:	CC-E I/I
Product ID:	1SVR011718R2500
EAN:	4013614351587
Catalog Description:	CC-E I/I Signal converter, singlef. 4-20mA / 4-20mA, 24VDC
Long Description:	The CC-E I/I is a single-function standard analog signal converter from the CC-E range. This converter, with 3-way electrical isolation, operates with a rated control supply voltage of 24 V DC. It provides an input signal range of 4-20 mA and an output signal range of 4-20 mA. Applied supply voltage is displayed by a green LED.

## Categories

Products » Low Voltage Products and Systems » Control Products » Signal Converters » Analog Signal Converters

## Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085
EAN:	4013614351587

## Container Information

Package Level 1 Width:	81 mm
Package Level 1 Length:	27 mm
Package Level 1 Height:	109 mm
Package Level 1 Gross Weight:	0.099 kg
Package Level 1 Units:	1 piece

## Dimensions

Product Net Height:	75 mm
Product Net Depth:	107 mm
Product Net Weight:	0.085 kg
Product Net Width:	22.5 mm

## Technical

Input Signal:	4 ... 20 mA
Output Signal:	4 ... 20 mA
Rated Control Supply Voltage (U <sub>S</sub> ):	24 V DC
Function:	Standard signals Single-function

## Environmental

RoHS Status:	Following EU Directive 2011/65/EC
--------------	-----------------------------------

## Certificates and Declarations (Document Number)

Instructions and Manuals:	1SVC011700M9000
cUL Certificate:	cUL508_E174460
Data Sheet, Technical Information:	2CDC110004C0209
Declaration of Conformity - CE:	1SVD981003-0000
RoHS Information:	1SVD981001-4400
UL Certificate:	UL508_E174460

## Classifications

ETIM 4:	EC002653 - Isolation amplifier
ETIM 5:	EC002653 - Isolation amplifier
ETIM 6:	EC002653 - Isolation amplifier
eClass:	7.0 27210120
UNSPSC:	39120000
Object Classification Code:	T

