

General Information

Extended Product Type:	OHB125J12
Product ID:	1SCA022381R1560
EAN:	6417019139159
Catalog Description:	OHB125J12 Handle
Long Description:	Handle

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories
Products » Low Voltage Products and Systems » Switches » Switch Fuses Accessories » Accessories for Switch Fuses

Ordering

EAN:	6417019139159
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85381000

Dimensions

Product Net Width:	158 mm
Product Net Height:	66 mm
Product Net Length:	160 mm
Product Net Depth:	45 mm
Product Net Weight:	0.16 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	160 mm
Package Level 1 Gross Weight:	0.16 kg
Package Level 1 EAN:	6417019139159

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Length:	125 mm
Handle Type:	Pistol
Order Multiple:	1 piece
Product Main Type:	OHB125J12
Product Name:	Handle
Product Type:	OHB
Special Functions:	J12
Suitable For:	OT630...800
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390010D0201

Classifications

E-number:	3171402
ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

