



## Datasheet for part number DAMAME26SF0

|  |                         |                     |              |
|--|-------------------------|---------------------|--------------|
| Our Catalog Part Number: DAMAME-26S-F0 |                         |                     |              |
| Brand: Cannon                          | Product Category: D Sub | Product Line: D Sub | Series: D*MA |

| Product Datasheet               |  |
|---------------------------------|--|
| General                         | D*M High reliable D-Sub Connectors with crimp termination        |
| Wire Gauge Range AWG            | Standard: AWG 20-28. High Density: AWG 22-28                     |
| Mating Cycles                   | 500  |
| Contact Arrangement             | Standard: 26 contacts size 20. High Density: 26 contacts size 22 |
| Dielectric Withstanding Voltage | 1000 VAC at sea level  |
| Current Rating                  | 7.5 A max  |
| Contact Resistance              | 10 milli Ohm max   |
| Operating Temperature           | -55°/+150°   |
| Salt Spray Test                 | 48 hours {96 Hrs for Stainless Steel}                            |
| Shell Material                  | steel  |
| Shell Finish                    | Yellow chromate over zinc  |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                                 |
| Insulator Color                 | black  |
| Gender                          | Socket   |
| Contacts                        | delivery without contacts, please order separately               |
| Contact Type                    | Crimp  |
| Contact Material                | copper alloy   |
| Contact Finish                  | gold over nickel (Performance Class 2)                           |
| Hardware                        | 4-40 Clinchnut   |