



Datasheet for part number DAMY3WK3SA197

|                                          |                                                                 |
|------------------------------------------|-----------------------------------------------------------------|
| Our Catalog Part Number: DAMY-3WK3S-A197 |                                                                 |
| Brand: Cannon                            | Product Category: D Sub   Product Line: D Sub   Series: COMBO D |

| Product Datasheet               |                                                           |
|---------------------------------|-----------------------------------------------------------|
| General                         | Combo D Series: D-Subminiature offering mixed layouts     |
| Wire Gauge Range AWG            | AWG 8-26                                                  |
| Contact Arrangement             | 3WK3 (3 empty size 8 cavities)                            |
| Dielectric Withstanding Voltage | 500 VAC at sea level                                      |
| Current Rating Signal Contacts  | 7.5 max                                                   |
| Operating Temperature           | -55°/+125°                                                |
| Salt Spray Test                 | 20 hours                                                  |
| Shell Material                  | steel                                                     |
| Shell Finish                    | pure tin over nickel                                      |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black                                                     |
| Gender                          | Socket                                                    |
| Contacts                        | delivery without size 8 contacts, please order separately |
| Mounting Method                 | Dual Float Mount                                          |