

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300190018](#)
Status: **Active**
Description: Die Block 4 Pole Angle Receptacle, Orange

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E46237
General	
Product Family	Industrial Receptacles
Series	130019
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678843301
Physical	
Coupling Type	Push to Lock
Gender	Female
Keyway	N/A
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	N/A
Orientation	N/A
Panel Mount	N/A
Poles	4
Temperature Range - Operating	N/A
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC
Material Info	
Old Part Number	43301
Reference - Drawing Numbers	
Sales Drawing	SD-130019-004

Image coming soon

Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Relevant

Search Parts in this Series
[130019](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION