



Datasheet for part number NPFFT-3-GY-L-T6

| |
|--|
| Our Catalog Part Number: NPFFT-3-GY-L-T6 |
| Our Global Manufacturing Part Number: AN026412G |
| Brand: Cannon Product Category: Circular Product Line: Veam Powerlock & Snaplock Series: POWERLOCK |

| Product Datasheet | |
|-------------------------------------|---|
| Series | Panel Drain (female contact) |
| Shell Style | Phase 3 |
| Color | Grey |
| Locking Type | Secondary Locking pin fitted to Drain Connector |
| Contact Type | 660A threaded post M12 (panel connector) |
| Maximum current rating | 660 A |
| Maximum rated voltage to earth | 2KVac / 3KVdc |
| Minimum flashover | 9.5K Vdc or Ac peak |
| Operating temperature range | -30°/+125° |
| Insulation resistance | <5 M ohms @500Vdc |
| Ingress protection (mated) | IP67 |
| Protection against electrical shock | IP2X |
| Flammability | UL94-V0 |
| Contact Retention | Nylon Pin |
| Mating Method | Bayonet |
| Mating Cycles | 500 |
| Operating Voltage | 1000Vac |
| Shell Material Finish | High temperature thermoplastic |