



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	60 A
System Voltage	240 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	None

### Complementary

Short Circuit Current Rating	10 kA
Number of Spaces	3
Wire Size	AWG 8...AWG 2 (copper or aluminium)

### Environment


Certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

### Ordering and shipping details

Category	00012 - QO 3 POLE CIRCUIT BREAKER
Discount Schedule	DE2A
GTIN	00785901400844
Nbr. of units in pkg.	3
Package weight(Lbs)	0.8300000000000007

Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------