



EMC instrument case Vario-Case iS

Instrument case for slide-in equipment, 482.6 mm (19") and modular assemblies.
Width: 534 mm

Material:

Side panels:
Extruded aluminium section, chromated on the inside, painted on the outside

Cover trays:

Plastic to UL 94-V0 (self-extinguishing), with a conductive coating on the inside

Rear panel: 2 mm aluminium, clear-chromated

Front panel: 2 mm aluminium, clear-chromated

Surface finish:

Clear-chromated/spray-finished, RAL 7030/7035

Supply includes:

2 plastic cover trays,
8 enclosure feet (12 with 400 mm depth),
2 side panels,
1 rear panel,
1 front panel,
4 mounting flanges, 482.6 mm (19"),
4 tapped strips,
4 untapped strips,
assembly parts.

HP	U	Height mm	Depth mm	Model No. VC
84	4	208.10	300	3743.700
84	7	341.40	400	3774.700
84	3	163.65	300	3733.700
84	3	163.65	400	3734.700
84	6	297.00	400	3764.700
84	6	297.00	500	3765.700
84	9	430.50	500	3795.700

Delivery times available on request.

EMC diagram,
see page 293.



EMC electronic Kombi system EL, 3-part

Material:

Wall unit and centre part:
1.5 mm sheet steel, yellow-passivated on the inside

Mounting plate:

2.75 mm sheet steel

Front door:

Extruded aluminium section, die-cast aluminium corner connectors, 4 mm safety glass, with EMC mesh.

Surface finish:

Textured stove enamel, enclosure RAL 7035, interior surfaces zinc-plated and passivated, door frame RAL 7033.

Protection category:

IP 55 to EN 60 529/10.91

Supply includes:

1 wall unit, solid,
2 gland plates, solid,
1 centre part, vertically hinged,
2 mounting angles, 482.6 mm (19"), fitted,
1 mounting plate, zinc-plated,
1 front door with EMC safety glass.

U	Width mm	Height mm	Depth mm	Model No. EL
3	600	212	415	2243.705
6	600	345	415	2246.705
9	600	478	415	2249.705
6	600	345	515	2256.705
9	600	478	515	2259.705
15	600	746	515	2265.705
21	600	1012	515	2271.705

Delivery times available on request.

Approvals,
see page 293.

EMC diagram,
see page 293.