

100-240VAC / 10A IEC Horizontal Rackmount Outlet Strip 1582E

Series



HAMMOND MANUFACTURING.



Features

- Rated 100-240VAC, 10A, 50/60Hz
- Designed for power distribution on front or rear of unit with IEC power cords.
- 1U horizontal 19" rackmount installation.
- All steel housing with black powder coat finish.
- On-Off switch is rocker type with green light (on those units with on-off switch) or a green pilot light to indicate power on.

Specifications

- Includes 10A circuit breaker to prevent accidental line overload.
- cULus listed to UL 60950-1 (2nd Edition); Amd1 + Amd2, and CAN/CSA
 C22.2 No. 60950-1-07 (2nd Edition); Amd1 + Amd2.
- TÜV certified to EN 60950-1:2006/A2:2013-09, and IEC 60950-1 (ed.2); am1;am2
- CE compliant to the European Low Voltage Directive 2014/35/EU.

Accessories

• Mounting Hardware

- Input Accessory Cords
- Rail Depth Adapter Kit
- RoHS

With Illuminated	Pilot								
On/Off Switch	Light Only	Overall Dimensions			Number of Outlets		Outlet	Inlet	Inlet
Part No.	Part No.	Height	Width	Depth	Front	Rear	Туре	Туре	Location
1582H8E1BK	1582T8E1BK	1.72	19.00	2.66	8	0	C13	C14	Rear
1583H8E1BK	1583T8E1BK	1.72	19.00	2.66	0	8	C13	C14	Rear

Data subject to change without notice

© 2016. Hammond Manufacturing Ltd. All rights reserved.