

Tube Axial Fans DNMF Series









Features

- Choice of 4.70" (120mm), 3.15" (80mm), 5.91" (150mm) or 10" (254mm).
- Choice of either 115 or 230 VAC, 50/60 Hz.
- Impedance protected motor.
- Class-B insulated.
- Ball bearing construction, metal or plastic blades.
- Diecast aluminum body.
- DNMF100AC, FAN150AC and FAN10A fans have male plug terminations (requires fan cords).
- FAN80AC fans have 11" long lead wires.
- Fan is cooled by incoming air.
- Fan component is recognized to UL 507 and CSA certified.
- Includes mounting hardware.

Accessories

• Fan Cords

• Filter Fan Grills

										Use With Fan	Use With Filter
Part No.	Part No.	Overall Dimensions				Wattage		Speed	Noise	Guard	Grill
115 VAC	230 VAC	Height	Width	Depth	CFM	50Hz	60Hz	(RPM)	(dB)	Part No.	Part No.
FAN80AC115	FAN80AC230	3.15	3.15	1.50	32	11	10	3100	34	FAN80FG	XPFA80*
DNMF100AC115	DNMF100AC230	4.70	4.70	1.50	105	24	22	3000	56	DNFG	XPFA120*
FAN150AC115	FAN150AC230	5.75 & 5.90	6.72	2.00 & 2.20	210 & 230	27 & 46	26 & 40	3100 & 3400	63 & 53	FAN150FG	XPFA150*
FAN10A115	FAN10A220	10.00	dia.	3.50	550	30	35	1650	60	FAN10FG	XPFA254*

Data subject to change without notice