



## Main

|                             |                      |
|-----------------------------|----------------------|
| Range of product            | Modicon M171/M172    |
| Product or component type   | Communication module |
| Communication port protocol | LonWorks             |


## Complementary

|                            |  |
|----------------------------|--|
| Integrated connection type | LON wire crimp - twisted pair  |
| Transmission rate          | 78 kbits/s   |
| Mounting adjustment        | Pitch 3.81 mm  |
| Electrical connection      | Removable screw terminal block   |
| Physical interface         | 90° insertion - 2.5 mm <sup>2</sup> cable                              |
| Supply                     | Via base board M171P/M172P   |
| Local signalling           | 1 LED red service<br>1 LED green status                                |
| Product compatibility      | Logic controller M172 performance<br>Logic controller M171 performance |
| Product weight             | 0.077 kg   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Product certifications                | CSA (pending)<br>CE<br>cURus (pending)<br>EAC (pending) |
| Marking                               | CE  |
| IP degree of protection               | IP20  |
| Ambient air temperature for operation | -10...55 °C   |
| Ambient air temperature for storage   | -20...85 °C   |
| Relative humidity                     | 10...90 % without condensation                          |

Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product   |
| RoHS (date code: YYWW)   | Compliant - since 1530 - Schneider Electric declaration of conformity<br> <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                    | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>  |